




SKU
MV-450-VG-115


Nombre del Proyecto:
Marca:
Enviado por:
Fecha: 07/10/2020

Energy Recovery Ventilator, Model MV-450, Direct Drive, with Vari-Green Motor, 115V



The MiniVent is an energy recovery ventilator designed for indoor installations in commercial and institutional applications. The compact design provides an economical solution for individual spaces, such as school classrooms and small offices and may be floor mounted or ceiling hung. A removable panel enables easy access to filters and enthalpy wheel.

- Energy efficient, Vari-Green motor
- Forward-curved blowers
- Galvanized steel construction
- Gravity backdraft dampers
- Single-point wiring
- Total enthalpy wheel certified to AHRI Standard 1060
- Speed controllable with a motor potentiometer or a 0-10 VDC Signal




A	B	C
37.6 in	26.34 in	19.9 in

Certifications

UL 1812
AHRI 1060

Características de funcionamiento



Características de Construcción

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Housing Material	Galvanized Steel
Includes	1 inch pleated filters
Certifications	UL 1812 AHRI 1060
Speed Controllable	Yes

Información del motor

Service Factor	1.25
Phase	1
Voltage	115
HP	1/4
Hertz	60
RPM	1800
Motor Insulation	B
Thermal Protection	Auto
Nominal Efficiency	85

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov