



SKU
872987

Job Name:
Mark:
Submitted By:
Date: 02/17/2020

Vari-Green Constant Pressure Control, Remote Transducer with Room Probe



The Constant Pressure Control can be used to monitor static pressure in a system, automatically adjusting the fan speed to maintain a desired static pressure. This control reduces energy consumption not only by reducing the speed and the energy used by the fan, but will also reduce the amount of conditioned air that is exhausted.

Recommended for use in multi-family structures, hotels and schools where demand control ventilation applications exist.

- 2-line, backlit display
- Dedicated airflow control mode
- NEMA-4 enclosure on all components
- Pressure range of +/- 1.0 inch wg
- Remote pressure transducer provides installation flexibility
- Intended for use with Greenheck's Vari-Green motor and Vari-Green Drive

Performance Characteristics

No Fan Curve Available.

Construction Features

Includes	(1) Room static probe Remote pressure transducer Vari-Green pressure control
----------	--

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov