



SKU
384903

Job Name:
Mark:
Submitted By:
Date: 03/05/2021

Vari-Green 2-Speed Control, with Digital Inputs



The two-speed control allows motor RPM (fan speed) to operate between two discreet speeds (A or B) through an SPDT switch or relay connected to the dry contact input or through wet voltage (115-230VAC) applied to the digital input terminal. This control accepts an input voltage of 115/208-240V and is intended for use with Greenheck's Vari-Green motor. Recommended for use in schools, restaurants, multi-family structures and condos where manual or demand controlled ventilation applications requiring high and low speed operation exist.

- Accepts input voltage of 85-277VAC
- Intended for use with Greenheck's Vari-Green motor and Vari-Green Drive

Performance Characteristics

No Fan Curve Available.

Construction Features

Includes

Vari-Green 2-speed control, with digital inputs

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov