



SKU
SP-A390-QD


Nombre del Proyecto:
Marca:
Enviado por:
Fecha: 11/17/2019

Ceiling Exhaust Fan, Model SP-A390, 115V, 1Ph, 279-410 CFM



Model SP-A direct drive, ceiling mounted fan is designed to provide the lowest sounds levels for bathroom exhaust. Units feature an insulated housing and are ideal for residential, multi-family or hotel applications.

- Acoustic insulation absorbs sound ensuring quiet operation
- Spring loaded aluminum backdraft damper eliminates rattling
- External electrical access reduces installation time
- Speed controllable
- Designer grille included




A	B	C	D	E
14 in	11.875 in	11.25 in	8 in	8 in

Certifications

AMCA Air & Sound
UL/cUL 507

Características de funcionamiento



Características de Construcción

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Housing Material	Galvanized Steel
Includes	Backdraft damper Mounting brackets
Certifications	AMCA Air & Sound UL/cUL 507
Speed Controllable	Yes

Información del motor

Service Factor	1
Phase	1
Voltage	115
Hertz	60
RPM	1300
Motor Insulation	B
Thermal Protection	Auto
Nominal Efficiency	38
Watts	57.2

Rendimiento de Aire y Sonido

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75
135	1350	1080	PCM	410	391	368	345	325	307	279
			Sones	4.5	4.5	4.5	5	5	5.5	5.5



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.