



SKU
SP-A50-90M-VG-QD

Nombre del Proyecto:
Marca:
Enviado por:
Fecha: 04/10/2021

Bathroom Exhaust Fan, Constant CFM with Motion Grille, Model SP-A50-90M, Vari-Green EC Motor, 115V, 1Ph, 50-90 CFM




Model SP-VG, bathroom exhaust fan features Vari-Green EC motor technology, allowing for increased energy savings. Units operate at a constant CFM up to 0.875 in. wg. And provide continuous or intermittent ventilation while maintaining extremely low sound levels. The motion sensor grille uses a passive infrared motion detector to automatically turn the fan on when a change in motion is sensed.

- Energy efficient Vari-Green motor
- ENERGY STAR rated
- Industry-leading low sound levels
- Units operate at a constant cfm up to 0.875 in. wg. and provides continuous or intermittent ventilation while maintaining extremely low sound levels
- Motion sensor grille included

Certifications

AMCA Air & Sound
UL/cUL 507



A	B	C	D	E
13.25 in	10.625 in	9 in	6 in	6 in

Características de funcionamiento

No hay curva del ventilador disponible.

Características de Construcción

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Housing Material	Galvanized Steel
Includes	Backdraft damper Mounting brackets Vari-Green EC motor. Motion grille
Certifications	AMCA Air & Sound UL/cUL 507
Speed Controllable	Yes

Información del motor

Service Factor	1
Phase	1
Voltage	120 230
HP	1/60
Hertz	60
Motor Enclosure	n/a
RPM	2300
Motor Insulation	B
Thermal Protection	Auto
Nominal Efficiency	1
Motor Included	Yes

Rendimiento de Aire y Sonido

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875
22.1	808	808	PCM	50	50	50	50	50	50	50	50
			Sones	<0.3	0.6	0.7	1.5	1.9	2	2.4	2.6
23.3	838	838	PCM	70	70	70	70	70	70	70	66
			Sones	<0.3	0.4	0.9	1.4	1.9	2.2	2.8	2.5
24.1	887	887	PCM	90	90	90	90	90	90	82	71
			Sones	<0.3	0.6	1	1.6	2.1	2.2	2.7	2.5

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov