




SKU  
SP-A110H-QD


Nombre del Proyecto:  
Marca:  
Enviado por:  
Fecha: 12/06/2019

# Bathroom Exhaust Fan with Humidity Sensor, Model SP-A110H, 115V, 1Ph, 98-130 CFM



Model SP-A direct drive, ceiling mounted fan is designed to provide the lowest sounds levels for bathroom exhaust. Units feature an insulated housing and are ideal for residential, multi-family or hotel applications. The humidity sensor automatically detects excess humidity in a space and activates the fan for control of excess moisture.

- Acoustic insulation absorbs sound ensuring quiet operation
- ENERGY STAR rated
- External electrical access reduces installation time
- Industry leading low sound levels
- Speed controllable
- Spring loaded aluminum backdraft damper eliminates rattling
- Humidity sensor to control excess moisture
- Designer grille included




A	B	C	D	E
13.25 in	10.625 in	9 in	8 in	6 in

## Certifications

AMCA Air & Sound  
UL/cUL 507

## Características de funcionamiento



## Características de Construcción

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Housing Material	Galvanized Steel
Includes	Backdraft damper Designer Grille Mounting brackets Humidity sensor
Certifications	AMCA Air & Sound UL/cUL 507
Speed Controllable	Yes

## Información del motor

Service Factor	1
Phase	1
Voltage	115
Hertz	60
RPM	950
Motor Insulation	A
Thermal Protection	Auto
Nominal Efficiency	24
Motor Included	Yes
Watts	18.5

## Rendimiento de Aire y Sonido

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25
19.4	950	760	PCM	130	115	98
			Sones	<0.3	<0.3	1.5