



SKU
CSP-A290-QD


Nombre del Proyecto:
Marca:
Enviado por:
Fecha: 06/17/2019

Inline Cabinet Fan, Model CSP-A290, 115V, 1 Ph, 77-318 CFM



Model CSP inline fans are high performance fans designed for exhaust, supply or return air applications where low sound level are required. Units feature an insulated, galvanized steel housing with a forward-curved wheel.

- Acoustic insulation absorbs sound for quiet operation
- Vertical electrical access to eliminate drilling holes
- Large electrical junction box for easy wiring
- Adjustable mounting brackets for multiple installation conditions
- Embossed, galvanized steel housing for rigidity
- Speed controllable motor
- Easy access to internal components through access panels




A	B	C	D	E	F	G
14 in	11.8 75 in	11.2 5 in	8 in	8 in	12.8 75 in	10 in

Certifications

AMCA Air
UL/cUL 507

Características de funcionamiento



Características de Construcción

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Housing Material	Galvanized Steel
Includes	Access Panel Backdraft damper Mounting brackets
Certifications	AMCA Air UL/cUL 507
Speed Controllable	Yes

Información del motor

Service Factor	1
Phase	1
Voltage	115
Hertz	60
RPM	1050
Motor Insulation	B
Thermal Protection	Auto
Nominal Efficiency	23
Watts	22

Rendimiento de Aire y Sonido

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875
102	1050	840	PCM	318	293	266	248	230	201	145	77
			Sones	1.6	1.9	2.7	3.4	4.1	3.7	3.9	4.8